Product Information - ITM-4

FOOD


"ITM-4" 4-Beam Turbidity Meter

Introduction

The Anderson-Negele ITM-4 Turbidity meter offers precision measurement of suspended solids through the use of infrared light. Utilizing a 4-beam technology the ITM-4 has multiple emitters and receptors to produce an online, real-time measurement of turbidity that can yield information critical to both process function and product quality. The compact integral design makes installation and set-up easy. But this simplicity in design does not mean that the ITM-4 is short on features. There are standard switching and analog (4-20mA) outputs along with 4 remote selectable ranges that are available to handle different products on the same process line.

Specifying the ITM-4 is easy with the line connection size as the only decision that needs to be made. Configuration is done with a simple three button navigation of the on-screen menus that makes selecting units of measure, analog output range, and switch point for your product a quick task. Most important to food and dairy processors is the robust design which offers lower cost of ownership than many other turbidity meters. The LED lamp technology provides longer life than devices utilizing tungsten bulbs and a sapphire lens is resistant to damage commonly found on other lens materials. Since this unit employs multiple beams, fouling of the optics is compensated automatically which significantly reduces the need for servicing. Most importantly the construction is the same rugged watertight stainless steel construction you have come to expect from Anderson-Negele. In fact the unit complies to the German IP69K standard which is more stringent that NEMA 4X. Whether the application involves alarming a process when signs of premature filtration failure occur or to provide constant feedback on a solids concentration to ensure product quality, the ITM-4 offers the needed performance and durability to give years of trouble free operation.

For more information on this turbidity meter, or any of our Anderson-Negele Instrument Products visit www.anderson-negele.com or call our customer service department at 1-800-833-0081



Authorizations



Features

- · 3-A Compliant; Third party verified in accordance with standard 46-03
- · 4-20 mA plus switch output
- · 4 Remote selectable ranges
- Ranges from 0-5 NTU to 0-5000
- 2 units (NTU and EBC) 11 ranges each

Applications

- · Whey/tower water monitoring
- · Chill water monitoring
- Filter monitoring
- · Yeast monitoring/dosing
- · Quality control
- · Waste water control

Specifications

Process Connection: 1.5", 2", 2.5", 3"

Installation: 5 pipe diameters before and 2 after

instrument

MATERIALS

Connection Head: SS 1.4305 (303 Stainless)

89 mm dia.

Fitting: SS 1.4404 (316L)

Optical Block: PEEK Lens: Sapphire

TEMPERATURE RANGES

Ambient: -10-60 °C (14-140°F)
Process: 0-100 °C (32-212°F)
CIP/SIP-Cleaning: up to 130 °C (266°F)
Operating Pressure: 145 psi maximum

Measurement Principle:

acc. to EN 7027 4-beam-altern. light

Wave Length:

acc. to EN 7027 860 nm ± 60 nm

LCD-Indicator

with Illumination: 2 x 8-digit
Accuracy: see table below

Electr. Connection:

Cable Entry: 2 x PG (M16 x 1.5)

Cable Connection: 2 x M12 plug-in(SS 316), (1) 4 pin,

(1) 5 pir

Supply Voltage: 24 ... (18-36 V DC) 160 mA maximum

INPUT

Input Range Switching: E1 and E2 24 ... (18-36 V DC) DC decoupled

Output

Analog: 4-20 mA active Short Circuit Proof: DC decoupled

Switching: 24 - 80 mA maximum respectively to GND

of power supply

MEASUREMENT RANGES

NTU: 0-5; 10; 20; 50; 100;

200; 500; 1000; 2000;4000; 5000 EBC: 0-1; 2; 5; 10; 20; 50;100;

200; 500; 1000;1250

Damping Time: 0; 1; 2; 4; 8; 16; 32; 64; 128 seconds

(adjustable)

APPROVALS

ETL Listed

Conforms to UL Std 61010-1 3rd Ed (with Display option B only)

Certified to CSA Std C22.2 61010-1 3rd Ed (with Display option B only)

ENVIRONMENTAL

Enclosure Protection: Design and tested to IP69k; intended for use

in wet environments at up to 100%

relative humidity

Total length of fitting(tol.: ±5/64")

Process connection / nominal width	Tri-Clamp®(-TC) acc. to DIN32676		
1.5"	11.33"		
2"	8.86"		
2.5"	6.75"		
3"	6.61"		


		Dip
total length	L	


Accuracy	at the calibration points	± 2%
-	(20; 200; 2000 NTU)	

	(20, 20	0, 2000 1110)		
Offset drift				< ± 0.3NTU (± 0.075EBC)
Slope accuracy	Range	0-1000 NTU	(0-250 EBC)	< 3 %
	Range	1001-2000 NTU	(250-500 EBC)	< 4 %
	Range	2001-5000 NTU	(500-1250 EBC)	< 6 %
Reproducibility	Range	0-1000 NTU	(0-250 EBC)	< 2 %
	Range	1001-2000 NTU	(250-500 EBC)	< 3 %
	Range	2001-5000 NTU	(500-1250 EBC)	< 4 %
Resolution	Range	0-100 NTU	(0-25 EBC)	0.1 NTU (0.025 EBC)
	Range	100-1000 NTU	(25-250 EBC)	1 NTU (0.25 EBC)
	Range	1001-5000 NTU	(250-1250 EBC)	10 NTU (2.5 EBC)


The following conditions must be met in order for the ITM-4 to comply with 3-A standard 46-03:

 The sensor must be mounted in a position that ensures it will be selfdraining.





Order Information



Accessories

Shielded cordset w/25' cable42117H0025Shielded cordset w/50' cable42117H0050Shielded cordset w/100' cable42117H0100Field Wireable Connector-Straight42119B0000Field Wireable Connector-90°42119A0000

05063 / 2.1 / 2015-03-20 / BK / NA

ANDERSON INSTRUMENT COMPANY 156 Auriesville Road Fultonville, NY 12072 Phone 800-833-0081 Fax 518-922-8997 info@anderson-negele.com

Tech. Support: techservice@anderson-negele.com Phone 800-833-0081